

Metal circular saw blade, HSS, coarse-toothed with taper tap and third tap, type C

for universal use up to 1000 N/mm² in larger cross sections and cutting depths on conventional machines

ORION[®]

Application:


For creating separation cuts in medium to large cutting depths in the material groups of steel, (stainless steel), cast iron and (non-ferrous metals) up to a strength of 1000 N/mm².

Execution:

- precision-ground metal circular saw blade with tooth type B, coarse serrated with taper tap and third tap, laterally hollow-ground, hole without keyway

Advantage:

- innovative cutting geometry with large chip space plus taper tap and third tap ensures cutting distribution and increases cutting performance
- top-quality cutting material for extremely demanding requirements in terms of service life
- universal use for a multitude of applications



| | |
|--|------------------|
| Art. no. | 14008 639 |
| Brand | ORION |
| Manufacturer Part Number | 14008639 |
| Tooth shape | C |
| Cutting material | HSS |
| Thickness of cutting edge | 4 mm |
| Tolerance of cutting edge diameter | js15 |
| Tolerance of cutting edge thickness | js11 |
| Tolerance of hole diameter | H7 |
| Cutting edge diameter | 160 mm |
| Bore diameter | 32 mm |
| Number of teeth | 48 PCS |
| DIN | 1838 |
| Form | C |
| Gross Weight | 0.564 kg |
| Product Group | 1QK |

EAN

4053625362554