

Collet chucks type ER25 in accordance with DIN 6499 A

UP = ultra precision, concentricity < 2 µm

ATORN[®]

Application

For use on precision collet chucks

Advantage

- Higher concentricity extends tool life

Art. No.	23388 188
Collet type	ER 25
Clamping diameter	10 mm
Min./max. clamping range	1-16 mm
Outer diameter	26 mm
Length	34 mm
Clamping bypass	-0.5 mm



EAN-Code

4050293631425