

shrink-fit extensions with IC

with straight shank

ATORN®

Application

For extending and reducing to smaller diameters.

Version

- With 4.5 ° angle
- Clamping diameter for shaft tolerance h 6
- Workpiece stop screw with 10 mm adjustment travel



Art. No.	23431 648
Clamping diameter	18 mm
Outer diameter	32 mm
Tapered diameter	27 mm
Length	150 mm
Max. clamp in depth	50 mm
Min. clamp in depth	40 mm
Max. adjustment travel	10 mm
Setting screw size	M10 x 1 mm
Width across flats	5 mm

EAN-Code

40502934 18293