

Precision scales 572

robust metal housing, bestseller for many applications

KERN

Application:

Versatile applications; suitable for use e.g. as laboratory scales, counting scales or check-weigher scales.

Execution:

- Robust metal housing
- LCD display with 14 mm digit size
- Automatic reference optimisation
- Mechanical overload protection
- Options: Battery operation
- Integrated KERN Universal Port (KUP): Connection of external KUP interface adapters, such as RS-232, USB, Bluetooth, Wi-Fi or Ethernet. (Adapter not included in scope of delivery.) This means that interfaces may easily be retrofitted without the need to open the scale housing and without complicated installation
- KERN Communication Protocol (KCP): The KCP allows for placing queries and remote control of the scale via external control units or computers

Advantage:

- User-programmable weighing unit (thread length g/m, paper weight g/m²)
- 572 model series scales can be integrated into the KERN Easy Touch system.

Delivery:

Mains adapter



| | |
|------------------------------------|-------------------|
| Art. no. | 44615 020 |
| Brand | KERN |
| Manufacturer Part Number | 572-45 |
| Type description | 572-45 |
| Max. weight measuring range | 12100 g |
| Digit increment, weight | 0.05 g |
| Plate size | 160 x 200 mm |
| With unit counting | Yes |
| Min. item weight | 0.15 g |
| Reproducibility | 0.05 g |
| Linearity | 0.15 g |
| Data transmission type | RS232 |
| Housing dimensions (LxWxH) | 310 x 180 x 90 mm |
| Gross Weight | 4.100 kg |
| Product Group | 447 |

EAN

4045761014282