

## Table scales FKB

**KERN**

### Application:

ideal for high-precision weighing in industrial environments

### Execution:

- Count resolution 360,000
- Housing with robust aluminium high-pressure die casting tub, ensures stable positioning, protects the weighing technology and is hard-wearing in everyday use
- Especially practical: Thanks to large weighing ranges and compact dimensions, heavy loads can be weighed with high precision even in the smallest of spaces. Useful for determining the most minute weight differences such as gas consumed, abrasion of mechanical parts, rock samples, minerals, druse, silver etc.
- PRE-TARE function for manual prior deduction of a known container weight, useful for fill level checks
- Freely programmable weighing unit, e.g. display directly in wire length g/m, surface weight g/m<sup>2</sup> (paper, fabric, sheet metal etc.) or similar
- with large weighing tray

### Delivery:

with power supply unit and work protection hood



<b>Art. no.</b>	<b>49000 036</b>
<b>Brand</b>	KERN
<b>Manufacturer Part Number</b>	FKB 65K0.2
<b>Type description</b>	FKB 65K0.2
<b>Max. weight measuring range</b>	65 kg
<b>Digit increment, weight</b>	0.2 g
<b>Digit height</b>	25 mm
<b>Plate size</b>	240 x 340 mm
<b>Material of cover panel</b>	Stainless steel
<b>With unit counting</b>	Yes
<b>Min. item weight</b>	2 g
<b>Reproducibility</b>	0.0002 kg
<b>Linearity</b>	0.001 kg
<b>Settling time scale</b>	3 s
<b>Data transmission type</b>	RS232
<b>Display type</b>	LCD
<b>Housing dimensions (LxWxH)</b>	350 x 390 x 120 mm
<b>Gross Weight</b>	7.600 kg
<b>Product Group</b>	447

### EAN

4045761103795