

Electronics side cutters

Round head with chamfer



Application:


For delicate cutting tasks in electronics and precision mechanics fields.

Execution:

- Ball bearing chrome steel
- Blades also inductively hardened
- Robust, box and clearance-free joint
- Low-friction double spring for smooth, even opening action

Advantage:

- Mirror-finished surface with fine oil film to protect against rust, no interference in the circuit by flaking chrome parts
- Safe, ergonomic and fatigue-free working thanks to two-component handles



Art. no.	53106 010
Brand	KNIPEX
Manufacturer Part Number	77 02 115
Length	116 mm
Max. soft wire diameter cutting capacity	1.6 mm
Head design	Round, With small bevel
Surface	Plain
Material of handle	2-component plastic
Gross Weight	0.075 kg
Product Group	535

EAN

4003773039334