

800pcs 2:1 Heat shrink tube-assortment


Item-No.: 22CA142 (1/2)

This range is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs. 800 pieces of shrinking ratio 2:1 standard shrinking tube for a range of application diameter from 1.5 to 12.0 mm.

The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used.



Shrinking ratio	2 : 1
Material	PE
Shrinking temperature	70°C - 110°C
Operation temperature	-40°C - 125°C
Flammability	VW-1
Tensile strength	≥ 10.4Mpa
Elongation at break	≥ 300%
Rated voltage	600V
Dielectric strength	≥ 1.5kv/mm at 30sec.
Volume resistivity	≥ 10 ¹⁴ Ω



set contents

Section	Heat shrink tube		Length	pcs
	Inner diameter ø	after shrink ø		
1-2	1.5 mm	0.85 mm	45 mm	150
3-4	2.5 mm	1.3 mm	45 mm	110
5	3.5 mm	1.8 mm	65 mm	60
6	5.0 mm	2.5 mm	65 mm	30
7	6.0 mm	3.0 mm	45 mm	25
8	8.0 mm	4.0 mm	45 mm	55
9	9.0 mm	4.5 mm	65 mm	55
10	12.0 mm	6.0 mm	65 mm	55


Heat shrink tube 2:1 assortment 620 pcs

Item-No.: 22CA142 (2/2)

This range is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs.

620 pieces of shrinking ratio 2:1 standard shrinking tube for a range of application diameter from 1.0 to 13.0 mm.

The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more.



Technical Specifications

Material: PE • Shrink ratio: 2:1 • Shrinking temperature: 80°C ... 125°C • Operation temperature: -20°C ... 130°C • Flammability: VW-1 • Tensile strength: 10 Mpa • Rated voltage: 600 V

Content

Quantity x Internal Diameter x Single Length x Color:

120pcs x 1.0mm x 45mm Black/ 95pcs x 1.5mm x 45mm Red / 75pcs x 2.0mm x 45mm Yellow / 55pcs x 2.5mm x 45mm Blue / 55pcs x 3.5mm x 45mm Green / 45pcs x 4.0mm x 45mm Red / 45pcs x 4.0mm x 45mm Black 35pcs x 5.0mm x 45mm Blue / 20pcs x 6.0mm x 45mm Blue / 30pcs x 7.0mm x 45mm Red 25pcs x 10.0mm x 45mm Black / 20pcs x 13.0mm x 45mm Black