



Sample photo

Order symbol: AB 050705
Product nbr: 7083520
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074003485
El. number:
Finland: 3423474
Denmark: 8212003208
Italy: 7311010

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		65	50	45	Ingress Protection (EN 60529): IP 66/67
inch:		2.6	2.0	1.8	Impact Resistance (EN 62262): IK 07
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:		Stainless steel			NEMA Class: NEMA 1, 4, 4X, 12, 13
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 80 °C			Gost R
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
TM 0505		Mounting plate			
TM 0507		Mounting plate			
TRM 0507		DIN-15 Mounting rail			
TF 28037		Wall fastening lug (4 pcs)			
TH A		Grey plastic hinges (2 pcs)			

