




EDOGF040MSS00.5E04 (M8)

Connection technology



1: O-ring

Product characteristics

Adapter socket

M8 connector

Electrical data

Electrical design

AC/DC

Operating voltage [V]

60 AC / 75 DC

Protection class

III

Environment

Ambient temperature [°C]

-25...85

Protection

IP 67

Mechanical data

Design

straight

Housing materials

Brass nickel-plated

Electrical connection



Connection

PVC cable / 0.5 m; 4 x 0.25 mm²

Wiring

Core colours

- BK black
- BN brown
- BU blue
- WH white



Remarks

Pack quantity [piece]

1