

M12 FEMALE FLANGE PLUG D CODED

PE-wires 4X0.34 0.2m

Flange M12 female, CAT 5
with multi-strand wire
D-coded, 4-pole, shielded
Front mounting


[Link to Product](#)

Illustration



Female





Product may differ from Image

Form

14501

Technical Data

Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

Cables

Cable number	976
No./diameter of wires	4 × 0.34 mm ²
Wire isolation	PE (wh, ye, bl, or)
C-track properties	2 Mio.
Shore hardness outer jacket	70 ± 5D
Outer diameter	approx. 1.25 mm
Bend radius (fixed)	5 × outer Ø
Bend radius (moving)	15 × outer Ø
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-20...+60 °C

Commercial data

country of origin	DE
customs tariff number	85444290
minimum order quantity	1