

M23 FEMALE, 0° 19 POLE

PUR 16x0,34+3X0.75 GRAY, drag ch 15m

M23

Female straight

19-pole

19-pole used



for 8-way distribution boxes, 5-pole

Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)**Illustration**

15	white
7	gray/ pink
5	green
4	red/blue
16	yellow
8	white/ green
3	gray
14	brown/ green
17	pink
9	white/yellow
2	red
13	yellow/ brown
11	black
10	white/ gray
1	violet
18	gray/ brown
19	brown 1.0mm ²
6	blue 1.0mm ²
12	green/ yellow 1.0mm ²

Female



Product may differ from Image

Form

23251

Technical Data

Operating voltage	max. 125 V AC/DC
Operating current per contact	max. 10 A
Locking of ports	Screw thread M23 × 1 mm
Protection	IP67 inserted and tightened (EN 60529)

Cables

Cable number	398
No./diameter of wires	16×0.34 + 3×0.75 mm ²
Wire isolation	PVC
C-track properties	1 Mio.
Jacket Color	gray
Shore hardness outer jacket	85 ± 5A
Material (jacket)	PUR/PVC
Outer diameter	approx. 10.6 mm
Bend radius (fixed)	10 × outer Ø
Bend radius (moving)	12 × outer Ø
Temperature range (fixed)	-30...+80 °C
Temperature range (mobile)	-5...+70 °C

General data

Temperature range	-25...+85 °C, depending on cable quality
-------------------	--

Commercial data

country of origin	DE
customs tariff number	85444290
minimum order quantity	1