

WIRE CONNECTOR WITH CONTROL WIRE TAP 3 PCS.
ACCESSORY FOR: 3VA4/5 125



Model	
Product brand name	SENTRON
Product designation	accessories






Connections according IEC	
Connectable conductor cross-section	
<ul style="list-style-type: none"> • for copper cable / solid / minimum • for copper cable / solid / maximum • for copper cable / finely stranded / minimum • for copper cable / finely stranded / maximum • for copper cable / stranded / minimum • for copper cable / stranded / maximum • for aluminum cable / solid / minimum • for aluminum cable / solid / maximum • for aluminum cable / stranded / minimum • for aluminum cable / stranded / maximum 	<ul style="list-style-type: none"> 1.5 mm² 6 mm² 1.5 mm² 95 mm² 1.5 mm² 95 mm² 1.5 mm² 6 mm² 1.5 mm² 95 mm²
Wire stripping length	12,2 mm
Tightening torque / when using copper cables	

- solid
 - <= 2.5 mm²: 2.8 Nm.
 - <= 6 mm²: 4.0 Nm,
 - <= 10 mm²: 6.2 Nm,
 - > 10 mm²: 11 Nm
- stranded
 - <= 2.5 mm²: 2.8 Nm.
 - <= 6 mm²: 4.0 Nm,
 - <= 10 mm²: 6.2 Nm,
 - > 10 mm²: 11 Nm
- finely stranded
 - <= 2.5 mm²: 2.8 Nm.
 - <= 6 mm²: 4.0 Nm,
 - <= 10 mm²: 6.2 Nm,
 - > 10 mm²: 11 Nm

Connections according UL

Wire stripping length	0.5 in
Connectable conductor cross-section	
• for copper cable / solid / minimum	14 AWG
• for copper cable / solid / maximum	10 AWG
• for copper cable / stranded / minimum	14 AWG
• for copper cable / stranded / maximum	3/0 AWG
• for copper cable / finely stranded / minimum	14 AWG
• for copper cable / finely stranded / maximum	3/0 AWG
• for aluminum cable / solid / minimum	12 AWG
• for aluminum cable / solid / maximum	10 AWG
• for aluminum cable / stranded / minimum	12 AWG
• for aluminum cable / stranded / maximum	3/0 AWG
Tightening torque / when using copper cables	
• solid	<= 12 AWG: 25 lb-in, <= 10 AWG: 35 lb-in, <= 8 AWG: 55 lb-in, > 8 AWG: 100 lb-in
• stranded	<= 12 AWG: 25 lb-in, <= 10 AWG: 35 lb-in, <= 8 AWG: 55 lb-in, > 8 AWG: 100 lb-in
• finely stranded	<= 12 AWG: 25 lb-in, <= 10 AWG: 35 lb-in, <= 8 AWG: 55 lb-in, > 8 AWG: 100 lb-in

Certificates

General Product Approval	EMC	Declaration of Conformity	other
 CSA	 UL	 EAC	 RCM
		 EG-Konf.	Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9133-0JG11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9133-0JG11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9133-0JG11

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

08/28/2017