



Strom
Current
Spannung
Voltage
Frequenz
Frequency

Wandgerätestecker
Wall mounting plug

IP 44

Anbaugerätestecker
Plug for mounting on machines and equipment

IP 44

Isogekapselt Schraubanschluss · In plastic enclosure screwed connection

A	V	Hz	Typ Type	Best.-Nr. Ref. No.	VPE PU	Typ Type	Best.-Nr. Ref. No.	VPE PU
16	400	50/60	CG 516/6h	2 125	10	CGT 516/6h	312 563	10
32	400	50/60	CG 532/6h	2 130	10	CGT 532/6h	56 550	5

5-polig *poles:*
3 P + N + ⊕



Wandgerätestecker
Wall mounting plug

IP 44

Phasenwender, isogekapselt Schraubanschluss · Phase inverter, in plastic enclosure screwed connection

A	V	Hz	Typ Type	Best.-Nr. Ref. No.	VPE PU
16	400	50/60	CGP 516/6h	94 762	10
32	400	50/60	CGP 532/6h	93 451	5

5-polig *poles:*
3 P + N + ⊕



Stecker Plug

IP 67

Kupplungsdose Coupler

IP 67

Isogekapselt Schraubanschluss · In plastic enclosure screwed connection

A	V	Hz	Typ Type	Best.-Nr. Ref. No.	VPE PU	Typ Type	Best.-Nr. Ref. No.	VPE PU
16	400	50/60	CTW 516/6h	55 242	10	CCW 516/6h	55 256	10
32	400	50/60	CTW 532/6h	55 245	10	CCW 532/6h	55 259	10
63	400	50/60	CTW 563/6h	15 334	2	CCW 563/6h	15 340	2
125	400	50/60	CTW 5125/6h	39 202	2	CCW 5125/6h	42 582	2

5-polig *poles:*
3 P + N + ⊕



IP 67

Wandsteckdose mit Klemmenleiste
Wall mounting socket with terminal bar

Isogekapselt Schraubanschluss · In plastic enclosure screwed connection

A	V	Hz	Typ Type	Best.-Nr. Ref. No.	VPE PU
16	400	50/60	COW 516/6h	313 176	1
32	400	50/60	COW 532/6h	313 173	1
125	400	50/60	COW 5125/6h	39 201	1

5-polig *poles:*
3 P + N + ⊕