

Accessory

PICO-LPG-660
Order Number: 70140347

Main Parameters (*)	min	typ	max	Unit
Operating Temperature	-50		85	°C
Storage Temperature	-50		80	°C

Main Data

Warranty 1 years

Technical Parameters

RoHS yes

Optical Parameters

Luminous transmittance	35.00 %
LB Rating	180-315 D LB6 + R LB4, >315-400 DR LB4, >615-660 DIR LB3, >660-665 DIR LB4, >665-715 D LB4 + IR LB5, 694 IR LB7
Lens Color	Blaugrün

Mechanical Parameters

Size	144x145x50 mm
Material	Polymer
Housing Color	black
Weight	10 g

(*) Over the complete operating temperature range

Features




- Complete protection
- Comfortable fit over prescription glasses or alone
- Adjustable temples and Side-shields for wide field of view
- CE Certified EN 207
- With Picotronic Logo imprint

Picture



Safety Label



Valid Revision

| 12-FEB-2021