

6 ft DVI-I Dual Link Digital/Analog Flat Panel Cable M-M*StarTech ID: DVIIDMM6*

Easily connect your PC or Mac computer to flat panel displays, digital CRT displays, projectors and HDTV without losing any signal quality with StarTech.com's DVI analog and digital display dual-link cables. With a faster, stronger signal than standard VGA monitor cables, DVI dual-link cables mean crystal-clear digital images instantly. Our DVI dual-link cables are available in 6, 10, 15 and 20 feet lengths and allow high-speed data transmission of up to 9.9 Gbits/sec.

Applications and Solutions

- > Compatible with Flat Panel Displays, Digital CRT Displays, Projectors and HDTV
- > Easily connect your PC to a HDTV, Projector and CRT Displays

Features

- > Compatible with PC and Mac computer systems
- > Compliant with DVI DDWG Standards
- > Dual link digital signalling allows high speed digital data transmission
- > DVI-I Dual Link Display Cable supports both analog and digital displays
- > High speed digital transmission rate of up to 9.9 Gbits/sec
- > Supports hot plugging of DVI display devices



The StarTech.com

Advantage:

Support and Resources: Single point of contact for all your questions; exclusive online tools and free live technical support

Save Time Sourcing: A complete selection of high-demand and hard-to-find products from one vendor

Best Value: StarTech.com products offer the best combination of features and price

Exclusive Resources: Complete product information and tools available at www.startech.com

Specifications

- > Connector A 1 - DVI-I Dual Link Male
- > Connector B 1 - DVI-I Dual Link Male
- > Color Black
- > Product Length 6 ft [1.83 m]
- > Maximum Cable Length 29.52 ft [9 m]
- > Carton Quantity 40
- > Shipping (Package) Weight 0.84 lb [0.38 kg]
- > Cable Length 6 Feet (3 Meters)
- > Cable Type DVI-I
- > Supported Type Analog & Digital
- > Compatibility PC and Mac
- > Connector A 28-pin digital DVI (Dual-Link) - male
- > Connector B 28-pin digital DVI (Dual-Link) - male
- > Compliant Standard DVI DDWG Standard
- > Color Black