

Beacon LED XXL

BEACON XXL MB 3K L3 WHT

2093005



Product features

- 2093005 BEACON XXL MB 3K L3 WHT Integrated LED spotlight, white RAL 9016, compact and minimalist design, ideal for double height spaces, retail and display applications, die-cast aluminium body, passive cooling heatsink, beam angle: 50° medium beam, optics: Silicone lens for controlled beam, colour temperature: 3000K warm white, total system power: 48W, total fixture output: 3670lm, luminaire efficacy: 76lm/W, LOR: 100%, colour rendering: Ra 93 typical, LED Chromacity: 3 step MacAdam ellipse, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: 1200mA, electronic driver, non-dimmable, switched only, power factor: 0.98 electrical protection: CLASS I, 3-circuit track adaptor, suitable for Concord Lytespan 3 track, ingress protection rating: IP20, suitable for internal environment only, horizontal rotation: 355°, vertical tilt: 90°, lockable positioning using Allen key, dimensi...



PRODUCT OVERVIEW

Product name	BEACON XXL MB 3K L3 WHT
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Retail
ETIM Class	EC001744
E-number FI	4278677
E-number SE	7401084
Warranty	5 years
Fixture luminous flux (lm)	3670
Luminaire efficacy (lm/W)	76.46
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	93
Colour Consistency (SDCM)	3
Beam Angle (°)	50
Photobiological Risk Group	RG1
Total power consumption (W)	48
Product Voltage (V)	240
Electrical protection	Class I
Control gear type	Electronic ballast
Dimming method	N/A
Housing colour	White
IP rating	IP20
Product EAN number	5025768930050

Beacon LED XXL

BEACON XXL MB 3K L3 WHT
2093005

DATA TABLE

General data

Product name	BEACON XXL MB 3K L3 WHT
Technology	LED
Housing	Aluminium
Mount	Track mounting
Environment	Internal
General application	Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
E-number FI	4278677
E-number SE	7401084
Warranty	5 years

Optical data

Fixture luminous flux (lm)	3670
Luminaire efficacy (lm/W)	76.46
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	93
Colour Consistency (SDCM)	3
Adjustable chromaticity	N
Beam Angle (°)	50
Photobiological Risk Group	RG1

Electrical data

Total power consumption (W)	48
Mains voltage (V)	220-240V
Product Voltage (V)	240
Lamp power factor	0.98
Electrical protection	Class I
Control gear type	Electronic ballast
Transformer required	Yes
Dimming method	N/A
Drive current (mA)	1200
Energy Efficiency Class (A->G) of contained light source	E

Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	55500

Physical data

Housing colour	White
IP rating	IP20


Beacon LED XXL BEACON XXL MB 3K L3 WHT 2093005

Diffuser finish	Diffuse
Reflector finish	None
Nominal Product Length (mm)	85
Nominal Product Width (mm)	168
Nominal Product Height (mm)	205
Nominal Product Diameter (mm)	113
Weight (kg)	1.5

Packaging

Single packaging type	Carton
Product EAN number	5025768930050
Packaging single length / height (cm)	25.0
Packaging single width (cm)	19.5
Packaging single depth (cm)	20.0
DUN14 (outer)	05025768930050
Units per outer package	1
Packaging outer length / height (cm)	25.0
Packaging outer width (cm)	19.5
Packaging outer depth (cm)	20.0

PHOTOMETRY



Distance [m]	Cone diameter [m]	E ₀ [lx]	E ₁ [lx]	E ₂ [lx]
0.5	0.46	14401	24.8°	5307
1.0	0.92	3600	24.8°	1327
1.5	1.39	1600	24.8°	599
2.0	1.85	900	24.8°	337
2.5	2.31	576	24.8°	215
3.0	2.77	400	24.8°	150

Distance [m] Cone diameter [m] Illuminance [lx]
C0 - C180 (Half beam angle: 49.6°)

TECHNICAL DRAWINGS

