

Resisto MW

Resisto 1500 IP66 MW 4200lm 840

0010255



Product features

- Resisto, integrated LED weatherproof luminaire, with UV stabilized flat diffuser designed to achieve uniform lit appearance, optimise light output and to reduce glare. 301 stainless steel diffuser clips and fixing brackets for surface mounting. Polycarbonate housing and diffuser - no yellow discolouration over time. 4200lm; 30W; 140lm/W; 4000K; SDCM<5; non dimmable; CRI80; IP66; IK08; Class I; 69,000hrs (L80B20) lifespan; 1500mm x 89mm x 88mm; D-mark; MW On/Off.



PRODUCT OVERVIEW

| | |
|---------------------------------|---|
| Product name | Resisto 1500 IP66 MW 4200lm 840 |
| Technology | LED |
| Cap/Base | N/A |
| Housing | PC Polycarbonate |
| Mount | Ceiling recessed mounting, Wall surface mounted |
| General application | Logistics & Industry |
| ETIM Class | EC002892 |
| E-number FI | 4357065 |
| Warranty | 5 years |
| Fixture luminous flux (lm) | 4200 |
| Luminaire efficacy (lm/W) | 140 |
| Colour temperature (K) | 4000 |
| CRI (Ra) | 80 |
| Colour Variation Initial (SDCM) | SDCM5 |
| Colour Consistency (SDCM) | 5 |
| Beam Angle (°) | 110 |
| Glare control | < 23 |
| Photobiological Risk Group | RG1 |
| Total power consumption (W) | 30 |
| Electrical protection | Class I |
| Control gear type | LED driver constant current |
| Dimmable | No |
| Dimming method | N/A |
| LED Flickering Rate | Ultra low (5% or less) |
| Housing colour | Grey |
| IP rating | IP66 |
| IK rating | IK08 |
| Product EAN number | 5410288102559 |

DATA TABLE

General data

| | |
|--------------|---------------------------------|
| Product name | Resisto 1500 IP66 MW 4200lm 840 |
| Technology | LED |

Resisto MW

Resisto 1500 IP66 MW 4200lm 840

0010255

| | |
|---|---|
| Cap/Base | N/A |
| Housing | PC Polycarbonate |
| Mount | Ceiling recessed mounting, Wall surface mounted |
| General application | Logistics & Industry |
| Operating temperature range (°C) | -20°C...+40°C |
| Performance ambient temperature Tq (°C) | 25 |
| ETIM Class | EC002892 |
| E-number FI | 4357065 |
| Warranty | 5 years |

Optical data

| | |
|---------------------------------|---------|
| Fixture luminous flux (lm) | 4200 |
| Luminaire efficacy (lm/W) | 140 |
| Colour temperature (K) | 4000 |
| CRI (Ra) | 80 |
| Colour Variation Initial (SDCM) | SDCM5 |
| Colour Consistency (SDCM) | 5 |
| Beam Angle (°) | 110 |
| Distribution type | Diffuse |
| Glare control | < 23 |
| Photobiological Risk Group | RG1 |

Electrical data

| | |
|--|-----------------------------|
| Total power consumption (W) | 30 |
| Mains voltage (V) | 220-240V |
| THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x % | 20 |
| Electrical protection | Class I |
| Control gear type | LED driver constant current |
| No. Of switching cycles before premature failures | >50000 |
| Dimmable | No |
| Dimming method | N/A |
| Drive current (mA) | 350 |
| Inrush Current (A) | 5.5 |
| Inrush Duration (µs) | 20 |
| Glow Wire Test (°C) | 850 |
| Energy Efficiency Class (A->G) of contained light source | D |
| Nominal Frequency (Hz) | 50/60Hz |
| LED Flickering Rate | Ultra low (5% or less) |
| Max. Luminaires per 10A C Breaker | 41 |
| Max. Luminaires per 13A C Breaker | 53 |
| Max. Luminaires per 16A C Breaker | 65 |
| Max. Luminaires per 20A C Breaker | 82 |
| Max. Luminaires per 10A B Breaker | 41 |
| Max. Luminaires per 13A B Breaker | 53 |
| Max. Luminaires per 16A B Breaker | 65 |
| Max. Luminaires per 20A B Breaker | 82 |

Resisto MW

Resisto 1500 IP66 MW 4200lm 840

0010255

Lifetime data

| | |
|------------------|--------|
| Lifespan L70 B50 | 100000 |
| Lifespan L80 B20 | 69000 |
| Lifespan L90 B10 | 31000 |

Physical data

| | |
|-----------------------------|------------------|
| Housing colour | Grey |
| IP rating | IP66 |
| IK rating | IK08 |
| Diffuser finish | Frosted |
| Diffuser material | PC Polycarbonate |
| Nominal Product Length (mm) | 1500 |
| Nominal Product Width (mm) | 87 |
| Nominal Product Height (mm) | 80 |
| Weight (kg) | 1.92 |


Packaging

| | |
|---------------------------------------|----------------|
| Single packaging type | Carton |
| Product EAN number | 5410288102559 |
| Packaging single length / height (cm) | 150.5 |
| Packaging single width (cm) | 10.0 |
| Packaging single depth (cm) | 8.5 |
| DUN14 (outer) | 05410288102559 |
| Units per outer package | 1 |
| Packaging outer length / height (cm) | 150.5 |
| Packaging outer width (cm) | 10.0 |
| Packaging outer depth (cm) | 8.5 |

Safety data

| | |
|----------------------------------|--------|
| Optimal operating condition (°C) | -20-40 |
|----------------------------------|--------|

PHOTOMETRY



Resisto MW

Resisto 1500 IP66 MW 4200lm 840

0010255

TECHNICAL DRAWINGS

