



Gehäuse und Kugel
 Drehgriff
 Kugeldichtung
 Spindelabdichtung
 Mediums- und Umgebungstemperatur
 Betriebsdruck

Messing vernickelt
 Kunststoff
 PTFE
 NBR
 -10 °C bis +80 °C
 max. 10 bar

Mini-Kugelhähne mit Drehgriff									
Artikel Nr.	Ident Nr.	Gewinde	DN	SW mm	L mm	L1 mm	H mm	I mm	I1 mm
371.01	103347	Rp 1/8 innen	5,5	14	36,5	19,0	21,5	8,0	8,0
371.02	103348	Rp 1/4 innen	5,5	14	43,0	19,0	21,5	11,0	11,0
371.02-1	103349	Rp 3/8 innen	7	18	48,0	18,0	22,5	11,5	11,5
371.02-2	103350	Rp 1/2 innen	10	22	59,0	25,0	32,0	15,0	15,0
371.03	103351	R/Rp 1/8 außen / 1/8 innen	5,5	14	35,5	19,0	21,5	8,0	8,0
371.04	103352	R/Rp 1/4 außen / 1/8 innen	5,5	14	38,0	19,0	21,5	11,0	8,0
371.05	103353	R/Rp 1/4 außen / 1/4 innen	5,5	14	40,5	19,0	21,5	11,0	11,0
371.06	103354	R/Rp 3/8 außen / 1/4 innen	5,5	14	41,5	19,0	21,5	11,5	11,0
371.07	103355	R/Rp 3/8 außen / 3/8 innen	8	18	44,5	19,5	22,5	11,5	11,5
371.09	103356	R/Rp 1/2 außen / 1/2 innen	10	22	55,5	26,5	32,5	15,0	15,0



371.02



371.05