

Twist drill type N HSS, vaporised

for universal use up to 1000 N/mm²

ATORN[®]



Application

Standard geometry for universal use up to 1000 N/mm².

Version

- Twist drill with universal standard geometry

Advantage

- excellent all-round properties and precise cutting pattern
- universal use: minimises tool costs and improves flexibility
- Vaporisation ensures favourable adherence of coolant

Delivery

Packaging unit: drill Ø 1.0-6.0 mm = 10 pieces (price per piece)

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	30	20		10		40	60	50	35	30	20	20	10	25					

Art. No.	11056 044
Cutting material	HSS
Surface	Vaporised
Type	N
Angle of the tip	118 Degree
Tool holding device	HA parallel shank
Cutting edge diameter	1.70 mm
Chip flute length	50 mm
Length	76 mm
f steel 700	0.04 mm/U
DIN	340

EAN-Code

4050293030372