

Hydraulic pressure cylinder RC



Execution:

- Single-acting cylinder.
- Model RC 50 with stationary thrust piece, all other cylinders with interchangeable, grooved thrust piece.
- Operating pressure of 700 bar
- With spring return mechanism.
- With scraper ring (apart from model RC 50).
- Hard-chrome-plated piston rod.
- With retaining thread on cylinder head (except mod. RC 50).

Advantage:

- Suitable for universal use.
- Retaining ring prevents piston rod from being pushed out.

Delivery:

1x ENERPAC hydraulic pressure cylinder RC 51.



Art. no.	29501 070
Brand	ENERPAC
Manufacturer Part Number	RC256
Model	RC 256
Max. compressive force	232 kN
Lift height	158 mm
Oil capacity	525 cm ³
Construction height, retracted	273 mm
Weight	10 kg
Gross Weight	10.501 kg
Product Group	258