

## Column-mounted slewing jib crane ASSISTENT AS – complete set with chain hoist

Lives up to its name



### Application:

Perfect for halls/rooms with low ceilings.

### Execution:


- classification according to EN 13001 HC2 S2 HD2 for light industrial use
- power supply with round trailing cable
- lockable isolating switch
- Operating voltage: 400 V/50 Hz, control voltage: 24 V
- Electric chain hoist with manual sliding chassis – two-stage lifting speed
- Swivel range 180°

### Advantage:

- Solid construction
- Ideal for halls/rooms with low ceilings

### Delivery:

Incl. detailed documentation



<b>Art. no.</b>	<b>77110 029</b>
<b>Brand</b>	VETTER
<b>Manufacturer Part Number</b>	AW10-3,0+SIXX6F-HF
<b>Model</b>	ASSISTENT AW
<b>Type</b>	Console assembly A
<b>Load-carrying capacity</b>	1000 kg
<b>Overhang</b>	3000 mm
<b>Max. lift height</b>	5 m
<b>Design</b>	With electric chain hoist
<b>Lifting device design</b>	With electric chain hoist SiXX-HF
<b>Flange width</b>	120 mm
<b>Swivel range</b>	180 Degree
<b>Colour</b>	Daffodil yellow RAL 1007
<b>Surface</b>	Lacquered
<b>Operating voltage</b>	400 V
<b>Cable length</b>	3.8 m
<b>Weight</b>	184 kg
<b>Max. vertical force</b>	12 kN
<b>Max. horizontal force</b>	48 kN
<b>Gross Weight</b>	266.000 kg
<b>Product Group</b>	7EL