

PRODUCT SPECIFICATION

Brand	Kasp
Product Range	Laminated Padlock
Catalogue number	130
Date	16/09/2009


Range Description
Laminated padlocks

Features

- Hardened steel shackle – extra protection against hacksaw and cropping attacks
- Double bolted locking mechanism – extra strength to resist torsion and pull attacks
- Zinc plated steel laminated body extra strength and resistance to corrosion
- 8 Steel countersunk rivets (4 on 30mm) – extra strength over traditional locks
- 5 Pin cylinder with anti-pick mushroom pins – extra protection against picking
- Paracentric keyway extra protection against manipulation
- Weather rating: 2

These padlocks are supplied display packed in sealed blisters and individually boxed

2 keys are supplied with each lock



Item Number	Item Description	EAN No	Commodity code	Carton Qty
K13030D	Laminated padlock 30mm – display packed	5013969900897	83011000	6
K13030A1	Laminated padlock 30mm KA303001 – boxed	5013969900880	83011000	12
K13040	Laminated padlock 40mm – boxed	5013969900903	83011000	12
K13040D	Laminated padlock 40mm – display packed	5013969900934	83011000	6
K13040D2	Laminated padlock 40mm Twin pack –	5013969901870	83011000	6

	display packed			
K13040A1	Laminated padlock 40mm KA304001 – boxed	5013969900910	83011000	12
K13040A2	Laminated padlock 40mm KA304002 – boxed	5013969900927	83011000	12
K13040L40D	Laminated padlock 40mm long shackle – display packed	5013969900941	83011000	6
K13050	Laminated padlock 50mm – boxed	5013969900958	83011000	6
K13050D	Laminated padlock 50mm – display packed	5013969900989	83011000	6
K13050D2	Laminated padlock 50mm Twin pack – display packed	5013969901887	83011000	4
K13050A1	Laminated padlock 50mm KA305001 – boxed	5013969900965	83011000	6
K13050A2	Laminated padlock 50mm KA305002 – boxed	5013969900972	83011000	6
K13060D	Laminated padlock 60mm – display packed	5013969901009	83011000	6
K13060A1	Laminated padlock 60mm KA306001 – display packed	5013969900996	83011000	6
K13050DSL	Laminated shed lock 50mm	5013969900989	83011000	6
K13050DCLIP	Laminated shed lock clip strip 6 x K13050D	5013969902785	83011000	1

<p>Technical product information</p>	<p>Body – laminated steel, zinc plated</p> <p>Shackle- Hardened alloy steel, chrome plated</p> <p>Locking mechanism:</p> <p>30/40mm - Pin tumbler cylinder type, 4 pin cylinder, Brass pins – Top pin 4 is plain, top pins 1 to 3 are mushroom type.</p> <p>50/60mm - Pin tumbler cylinder type, 5 pin cylinder, Brass pins – Top pin 5 is plain, top pins 1 to 4 are mushroom type.</p> <p>Key differs:</p> <p>30mm – 202 40mm – 420 50/60mm – 1988</p> <p>Re-keyable – No</p> <p>Security rating:</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Item</th> <th>Security rating</th> </tr> </thead> <tbody> <tr> <td>K13030D</td> <td>4</td> </tr> <tr> <td>K13030A1</td> <td>4</td> </tr> <tr> <td>K13040</td> <td>6</td> </tr> <tr> <td>K1040D & D2</td> <td>6</td> </tr> <tr> <td>K13040A1</td> <td>6</td> </tr> <tr> <td>K13040A2</td> <td>6</td> </tr> <tr> <td>K13040L40D</td> <td>6</td> </tr> </tbody> </table>	Item	Security rating	K13030D	4	K13030A1	4	K13040	6	K1040D & D2	6	K13040A1	6	K13040A2	6	K13040L40D	6
Item	Security rating																
K13030D	4																
K13030A1	4																
K13040	6																
K1040D & D2	6																
K13040A1	6																
K13040A2	6																
K13040L40D	6																

K13050	7
K13050D & D2	7
K13050A1	7
K13050A2	7
K13060D	10
K13060A1	10
K13050DSL	7

Shackle Dimensions:

Dimensions mm	Shackle		
	Dia	Internal width	Internal height
K13030D	6	13	17
K13030A1	6	13	17
K13040	7	19	21
K13040D & D2	7	19	21
K13040A1	7	19	21
K13040A2	7	19	21
K13040L40D	7	19	38
K13050	9	23	29
K13050D & D2	9	23	29
K13050A1	9	23	29
K13050A2	9	23	29
K13060D	11	28	33
K13060A1	11	28	33
K13050DSL	9	23	29

Use environment- Normal outdoor use

Recommended applications- Garages, toolboxes, sheds, gates, lockers, shutters etc.

Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	These products do not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered
Country of origin	China

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
K13030D	34	20	50	105	140	25	170	134
K13030A1	34	20	50	105	38	23	55	110
K13040	44	25	65	224	50	25	70	231
K13040D	44	25	65	224	140	23	170	256
K13040D2	-	-	-	-	155	25	170	474
K13040A1	44	25	65	224	50	25	70	231
K13040A2	44	25	65	224	50	25	70	231
K13040L40D	44	25	80	232	140	22	190	265
K13050	53	29	80	383	58	33	83	393
K13050D	53	29	80	383	140	30	170	411
K13050D2	-	-	-	-	155	35	170	805
K13050A1	53	29	80	383	58	33	83	393
K13050A2	53	29	80	383	58	33	83	393
K13060D	63	32	93	608	150	30	190	651
K13060A1	63	32	93	608	70	38	100	622
K13050DSL	53	29	80	383	140	30	170	411
K13050DCLIP	-	-	-	-	-	-	-	-

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
K13030D	150	185	90	882		
K13030A1	80	155	55	1355		
K13040	105	170	70	2824		
K13040D	150	185	100	1622		
K13040D2	165	240	85	2946		
K13040A1	105	170	70	2824		
K13040A2	105	170	70	2824		
K13040L40D	145	230	95	1686		
K13050	110	125	85	2408		
K13050D	145	215	110	2566		
K13050D2	145	215	100	3306		

K13050A1	110	125	85	2408		
K13050A2	110	125	85	2408		
K13060D	160	250	120	4027		
K13060A1	125	145	100	3801		
K13050DSL	145	215	110	2566		
K13050DCLIP	145	45	960	2560		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
K13030D	22	Blister	7	Backing card			78	Box
K13030A1			5	Box			35	Box
K13040			7	Box			52	Box
K13040D	22	Blister	7	Box			86	Box
K13050D2	20	Blister	7	Backing card			102	Box
K13040A1			7	Box			52	Box
K13040A2			7	Box			52	Box
K13040L40D	25	Blister	8	Backing card			96	Box
K13050			10	Box			50	Box
K13050D	25	Blister	7	Backing card			100	Box
K13050D2	30	Blister	9	Backing card			86	Box
K13050A1			10	Box			50	Box
K13050A2			10	Box			50	Box
K13060D	30	Blister	13	Backing card			121	Box
K13060A1			13	Box			50	Box
K13050DSL	25	Blister	7	Backing card			100	Box
K13050DCLIP	132	Blisters	42	Backing cards	76	Bag & clip strip		