



REVISED	DR	APP



- Connections: USB 3.1 C plug to DVI 24+1 plug
- Resolution: up to 4K2K (30 Hz)
- Alternate Mode
- Plug: moulded
- Wire material: copper
- Plug material: nickel
- Contact surface: gold plated
- Color: black
- USB Type C reversible plug

NOTE :

- 3840×2160@30Hz resolution
- Operating Temperature:0℃~45℃
- Storage Temperature:-20℃~ 70℃
- ROHS 2.0 and Reach compliant.
- PACKING: 1pc/PE Bag+Label



⑨	DUST CAP	LD-PE	1	
⑧	THUMB SCREW	#4-40 GOLD PLATED MATERIAL SCREW, Ø3.95MM*L52.7MM, MOLDING BLACK	2	
⑦	HOUSING	ABS Black	1	
⑥	OUTER MOLD	PVC Black	1	
⑤	INNER MOLD	LD-PE	2	
④	PCBA	Type C to DVI PCBA	1	
③	DVI CONNECTOR	DVI-D(24+1) MALE, BLACK INSULATION, GOLD PLATED CONTACTS, GOLD SHELL+PCB	1	
②	USB C TYPE	USB C /M Solder Type, Black PBT Insulation, The Pin Gold Plating, the shell for Gold Plating	1	
①	CABLE	(1P*32#+D+AL+ML) *4+1P*32#+4C*32#+1C*22#+D+AL+B TPE/Black Jacket OD:4.5	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK



DESCRIPTION		USB 3.1 C plug - DVI 24+1 plug					
SIZE	A4	DATE	14.11.2018	CHECKED		TOL	
UNIT	MM	DRAWN	SIM	APPROVED			BS10-58025
CUSTOM TARIF NO.: 85444290							