

# KERN TD225-0.1US.

Kompaktes Materialdickenmessgerät mit externem Messkopf

**KERN**<sup>®</sup>



## Construction

Cable length:	90 cm
Casing material:	Plastic
Dimensions housing (WxDxH):	120 x 65 x 30 mm

## Measuring system

Measuring head diameter:	8 mm
Measuring range [Max]:	22,500 cm
Precision (of [Max]):	0,005
Readout [d]:	100 µm
Sound velocity (Max):	599,940 mm/min
Sound velocity (Min):	60 mm/min
Test frequency:	5 MHz
Weighing units:	mm

## Environmental conditions

Maximum operating temperature:	50 °C
Minimum ambient temperature:	0 °C

## Service

ISO calibration certificate:	961-113
------------------------------	---------

## Category

Brand:	Sauter
Category:	Material thickness gauges
Product Group:	Ultrasonic thickness gauge

## Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	265 x 215 x 63 mm
Gross weight:	750 g
Net weight:	164 g
Shipping method:	Parcel service