

motor operator 24-60V DC accessory for: 3VA2 100/160/250



Model	
Product brand name	SETRON
Product designation	Accessories
Product version	Motorized operating mechanism (MO)
Accessories	Motorized operating mechanism (MO)





Mechanical Design	
Rated control supply voltage U_s with DC	24 V
Height	75 mm
Width	104.6 mm
Depth	132 mm
Net weight	941 g
Connectable conductor cross-section / solid / minimum	1.5 mm ²
Connectable conductor cross-section / solid / maximum	2.5 mm ²
Connectable conductor cross-section / finely stranded / with core end processing / minimum	1.5 mm ²
Connectable conductor cross-section / finely stranded / with core end processing / maximum	2.5 mm ²

Ambient temperature / during operation	
• minimum	-25 °C
• maximum	70 °C
Ambient temperature / during storage	
• minimum	-40 °C
• maximum	80 °C

Connections according IEC

Wire stripping length	7 mm
-----------------------	------

Certificates

General Product Approval	EMC	Declaration of Conformity	Shipping Approval	other
Miscellaneous				
	RCM	EG-Konf.	LRS	Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9267-0HA10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9267-0HA10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9267-0HA10


CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





last modified:

11/17/2018