

Stackable 4 mm Banana Plug to Stackable 4 mm Banana Plug Lead



Features

Rear 4mm banana female connection to stack the plugs

Applications

To connect to 4mm banana jacks and binding points

Very low voltage general purpose electric testing, controlling and measuring



Specification

Electrical protection	33V AC/ 60V DC, 20 A
Operating Temperature Range	-20 °C...+80 °C

RND Part Nr.	Colour	Length
RND 350-00053	Red	1m
RND 350-00054	Black	1m
RND 350-00055	Blue	1m
RND 350-00056	Yellow	1m
RND 350-00057	Green	1m

