



## Main

|                                 |  |
|---------------------------------|--|
| Range of product                | Harmony XAC                                  |
| Product or component type       | Head for push-button                         |
| Component name                  | XACB   |
| Marking                         | Unmarked                                     |
| Operator additional information | Booted                                       |
| Operating travel                | 16 mm  |
| Cap/Operator or lens colour     | White  |
| Product compatibility           | XESD1181<br>XESD1191<br>XESD1281<br>XESD1291 |
| Sale per indivisible quantity   | 10   |

## Complementary

|                |          |
|----------------|----------|
| Product weight | 0.005 kg |
|----------------|----------|

## Environment

|                                       |   |
|---------------------------------------|---|
| Standards                             | EN 60947-5-1<br>IEC 60947-5-1<br>CSA C22.2 No 14    |
| Ambient air temperature for operation | -25...70 °C   |
| Ambient air temperature for storage   | -40...70 °C   |
| Vibration resistance                  | 15 gn (f = 10...500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance                      | 100 gn conforming to IEC 60068-2-27                 |
| Electrical shock protection class     | Class II conforming to IEC 61140                    |
| IP degree of protection               | IP65 conforming to IEC 60529                        |
| IK degree of protection               | IK08 conforming to EN 50102                         |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|