

- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

STANDARD EXECUTIONS

Aluminium, glossy finish:

- **GN 743-A:** with reflector made out of technopolymer (PSU polysulfone).
- **GN 743-B:** without reflector.

Black anodised aluminium:

- **GN 743-AS:** with reflector made out of technopolymer (PSU polysulfone).
- **GN 743-BS:** without reflector.

WINDOW

Natural glass.

RING

NBR synthetic rubber.

MAXIMUM CONTINUOUS WORKING TEMPERATURE


100°C.

FEATURES AND APPLICATIONS

GN 743 oil level indicators can be used on pressurised oil tanks (oil-proof resistance data available on request).

ACCESSORIES ON REQUEST

Brass nuts type GH. (see page 1574) (with Gas threadings only) for fitting to reservoirs with wall thickness smaller than 5 mm.



GN 743-A

GN 743-AS

Code	Description	Code	Description	d1	d2	d3	l1	l2	s	⚖
GN.37506	GN 743-7-M14X1,5-A	GN.37507	GN 743-7-M14X1,5-AS	7	M14X1,5	20	7.5	6.5	18	7
GN.37501	GN 743-11-M16x1.5-A	GN.37502	GN 743-11-M16X1,5-AS	11	M16x1.5	22	8	7.5	20	8
GN.37511	GN 743-14-M20x1.5-A	GN.37512	GN 743-14-M20X1,5-AS	14	M20x1.5	26	8.5	7.5	23	10
GN.37521	GN 743-18-M26x1.5-A	GN.37522	GN 743-18-M26X1,5-AS	18	M26x1.5	32	9	8	30	18
GN.37523	GN 743-18-M27x1.5-A	GN.37525	GN 743-18-M27X1,5-AS	18	M27x1.5	32	9	8	30	18
GN.37531	GN 743-24-M33x1.5-A	GN.37533	GN 743-24-M33X1,5-AS	24	M33x1.5	40	11	8.5	36	26
GN.37541	GN 743-32-M40x1.5-A	GN.37542	GN 743-32-M40X1,5-AS	32	M40x1.5	50	12	9	46	39
GN.37543	GN 743-32-M42x1.5-A	GN.37545	GN 743-32-M42X1,5-AS	32	M42x1.5	50	12	9	46	43
GN.37559	GN 743-7-G1/4-A	GN.37560	GN 743-7-G1/4-AS	7	G 1/4	20	7.5	6.5	18	8
GN.37561	GN 743-11-G3/8-A	GN.37562	GN 743-11-G3/8-AS	11	G 3/8	22	8	7.5	20	9
GN.37563	GN 743-14-G1/2-A	GN.37564	GN 743-14-G1/2-AS	14	G 1/2	26	8.5	7.5	23	11
GN.37565	GN 743-18-G3/4-A	GN.37566	GN 743-18-G3/4-AS	18	G 3/4	32	9	8	30	18
GN.37567	GN 743-24-G1-A	GN.37568	GN 743-24-G1-AS	24	G 1	40	11	8.5	36	26
GN.37569	GN 743-32-G1¼-A	GN.37570	GN 743-32-G1¼-AS	32	G 1 1/4	50	12	9	46	42
GN.37571	GN 743-32-G1½-A	GN.37572	GN 743-32-G1½-AS	32	G 1 1/2	60	13	9	55	45

GN 743-B

GN 743-BS

Code	Description	Code	Description	d1	d2	d3	l1	l2	s	⚖
GN.37606	GN 743-7-M14X1,5-B	GN.37607	GN 743-7-M14X1,5-BS	7	M14X1,5	20	7.5	6.5	18	7
GN.37601	GN 743-11-M16x1.5-B	GN.37602	GN 743-11-M16X1,5-BS	11	M16x1.5	22	8	7.5	20	8
GN.37611	GN 743-14-M20x1.5-B	GN.37612	GN 743-14-M20X1,5-BS	14	M20x1.5	26	8.5	7.5	23	10
GN.37621	GN 743-18-M26x1.5-B	GN.37622	GN 743-18-M26X1,5-BS	18	M26x1.5	32	9	8	30	18
GN.37623	GN 743-18-M27x1.5-B	GN.37625	GN 743-18-M27X1,5-BS	18	M27x1.5	32	9	8	30	18
GN.37631	GN 743-24-M33x1.5-B	GN.37633	GN 743-24-M33X1,5-BS	24	M33x1.5	40	11	8.5	36	26
GN.37641	GN 743-32-M40x1.5-B	GN.37642	GN 743-32-M40X1,5-BS	32	M40x1.5	50	12	9	46	39
GN.37643	GN 743-32-M42x1.5-B	GN.37645	GN 743-32-M42X1,5-BS	32	M42x1.5	50	12	9	46	43
GN.37659	GN 743-7-G1/4-B	GN.37660	GN 743-7-G1/4-BS	7	G 1/4	20	7.5	6.5	18	8
GN.37661	GN 743-11-G3/8-B	GN.37662	GN 743-11-G3/8-BS	11	G 3/8	22	8	7.5	20	9
GN.37663	GN 743-14-G1/2-B	GN.37664	GN 743-14-G1/2-BS	14	G 1/2	26	8.5	7.5	23	11
GN.37665	GN 743-18-G3/4-B	GN.37666	GN 743-18-G3/4-BS	18	G 3/4	32	9	8	30	18
GN.37667	GN 743-24-G1-B	GN.37668	GN 743-24-G1-BS	24	G 1	40	11	8.5	36	26
GN.37669	GN 743-32-G1¼-B	GN.37670	GN 743-32-G1¼-BS	32	G 1 1/4	50	12	9	46	42
GN.37573	GN 743-32-G1½-B	GN.37574	GN 743-32-G1½-BS	32	G 1 1/2	60	13	9	55	45

Accessories for hydraulic systems