


## Product information

# 97 53 18 SB

## KNIPEX Twistor®16

Self-Adjusting Crimping Pliers for wire ferrules  
With rotatable die head




- Crimp head can be rotated 360°, with 8 locking positions
- Square crimp profile, high capacity range from 0.14 to 16 mm<sup>2</sup>
- Wire ferrules can be crimped from almost any working position
- Crimping pliers adjust automatically to different cross-sections
- Crimp opening accessible from both sides, extra-long wire ferrules can be fed in
- Crimping of Twin wire ferrules up to 2 x 6 mm<sup>2</sup> possible
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Light and handy tool, manual force reinforced by toggle lever mechanism
- Special quality chrome vanadium electric steel, oil-hardened

### General

Article No.	97 53 18 SB
EAN	4003773082736
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	475 g
Dimensions	200 x 114 x 26 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

### Technical details



Application	Wire ferrules
Capacity in square millimetres	0.14 — 16 mm <sup>2</sup>
AWG	26 — 6
Number of crimping positions	1

*technical change and errors excepted*



Uniquely flexible: connectors can be inserted in the rotatable crimp head from almost any position



Twin wire ferrules up to 2 x 6 mm<sup>2</sup> can be crimped without adjustment





Crimp head can be rotated 360° for optimal accessibility, even in confined spaces