

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0191990011](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Butt - Window Splice for 10-12 AWG Wire

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">Product Specification PS-19902-011-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Splices
Series	19199
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<a href="#">Splices</a>
Product Name	Butt - Window
UPC	800753046849

**Physical**

Barrel Type	Closed
Color - Resin	Yellow
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	3.491/g
Packaging Type	Bag
Temperature Range - Operating	-55° to +105°C
Wire Insulation Diameter	5.79mm max.
Wire Size AWG	10, 12
Wire Size mm <sup>2</sup>	3.30-5.00

**Electrical**


Voltage - Maximum	300V
-------------------	------

**Material Info**

Engineering Number	WC-842
--------------------	--------

**Reference - Drawing Numbers**

Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19199-003



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[19199 Series](#)