

CONSTANT VOLTAGE LED DRIVER

12VDC 30 WATT



POWERPAX: LED-DR-12V-30W-SLIM

Features:

- Input Voltage 200-240 Vac
- IP20 Rated
- Class II
- Compact Plastic Low Profile enclosure
- 1 Year Warranty



Description:

The Range of 30 Watt Constant Voltage LED Drivers are housed in a compact light weight high quality IP20 plastic enclosure with covered input & output terminals suitable for general Indoor LED applications.

Specification	
Part Number	LED-DR-12V-30W-SLIM
Output Voltage Rating	12Vdc
Output Current	2.5A
Rated Power	30 W
Dimensions	251(L) x 39(W) x 16(H)mm
Input Voltage Range	200-240 VAC
Input Voltage Frequency	50-60Hz
Inrush Current	<60A
Input power	>0.9W
Efficiency	85%
Power Consumption Without Load	<0.5W
Overload Protection	Ta, input 0.94-1.06 times rated voltage output 1.1 times rated load
Short Circuit Protection	Ta, input 0.94-1.06 times rated voltage output short circuit for 1 hour
Automatically Restart	Yes
Working Temperature	-20°C to +45°C
Relative Humidity	45% to 85%
MTBF	30000hr
EMC emission	IEC55015
EMC Immunity	IEC61547
Safety Standards	EN61347-1, EN61347-2-13

POWERPAX

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


TT Electronics IoT Solutions Ltd
Tofts Farm East, Brenda Road, Hartlepool, TS25 2BQ, UK
t: +44 (0) 1429 852 500

CONSTANT VOLTAGE LED DRIVER

12VDC 30 WATT

POWERPAX: LED-DR-12V-30W-SLIM

Diagrams



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

POWERPAX