

Spring balances with load capacity of 2.0-14.0 kg, with automatic lock

Type 7222, cable extension 3000 mm, rustproof

AUTOSTAT

Application:

Can be used for the following tools and devices, e.g.: Electrical and compressed air hand machines, engravers, exhaust hoses, compressed air devices, paint spray guns, film welding devices

Advantage:

- Effortless work



Art. no.	77001 575
Brand	AUTOSTAT
Manufacturer Part Number	77001575
Min. load-carrying capacity	10 kg
Max. load-carrying capacity	14 kg
Type	7222
With automatic locking	Yes
Max. cable pull-out length	3000 mm
Adjustable cord length	No
Material of cord	Stainless Steel
Wire cable diameter	3 mm
Replaceable cord	Yes
Cord in-feed restriction	Absorbs impacts, adjustable
Material of cable drum	Abrasion-proof plastic
Suspension type	Freely rotating and pivot screw karabiner hook
Load attachment	Screw Karabiner hook
Material of housing	Plastic
Housing height	259.4 mm
Housing width	211.5 mm
Housing thickness	70 mm
Design	All external components made of non-rusting material
Height	550 mm
Spring design	Special mainspring
With overrotation protection	Yes
Spring breakage protection	Yes
Number of springs	1 PCS
DIN	15112
Gross Weight	4.000 kg
Product Group	7EB

EAN

4053625360192