

# Pin Headers

5.0/5.08mm pitch



## SPECIFICATION:

### Material

Pin Header	Brass, Tin Plated
Housing	PA66, UL94V-0

### Electrical

Standard	IEC	
Rated Voltage	300V	320V
Rated Current	15A	20A
Withstand Voltage	AC2000V/1Min	
Contact Resistance	20mΩ	
Insulation Resistance	500MΩ/DC500V	

### Mechanical

Temperature Range	-40°C~+105°C
Max Soldering	250°C for 5sec

### Size

Pitch	5.0mm (.197"), 5.08mm (.197")
Poles	2P-12P

