

BNC Adapter



Art.-No.	Description	PU
52522.1	Adapter 50 Ohm jack/jack	100
52523.1	Adapter 75 Ohm jack/jack	100
52518.1	T-Adapter 1 Plug / 2 Jack RG58 50 Ohm	100
52519.1	T-Adapter 2 Jack / 1 Plug RG59/62 75/93 Ohm	100
52524.1	Terminator 50 Ohm plug	100

BNC Crimping Tool for RG58/59/62



Crimping tool for RG58/59/62 coaxial connector

Art.-No.	Description
52535.2	BNC Crimping Tool for RG58/59/62

BNC Patch Cable



Stock length: 0,5 - 1,0 - 2,0 - 3,0 - 5,0 - 10 m

Pre-assembled RG58 coaxial cable for high frequent measured data and signals

Art.-No.	Description
K8300.x	Coax Cable RG58 C/U 50 Ohm 2x Plugs straight
K8360.x	Coax Cable RG59 75 Ohm 2x Plugs straight

BNC Boots



Strain relief boots for BNC crimp plugs
Colours: .1=black .2=red .3=blue .4=green

Art.-No.	Type	Min. inner diameter	PU
52527.x	RG58	5.0 mm	50
52529.x	RG59/62	6.5 mm	50
52537.x	RG174	2.8 mm	50

Stripping Tool RG58/59/62



Stripping tool for stripping of RG58/59/62 coaxial cable

Art.-No.	Description
52536.2	Stripping Tool for BNC RG58/59/62

Coaxial Cable Thin Wire RG58 C/U, 50 Ohm, double shielded



Drum sizes: 100 - 1000 m

Coaxial Thin Wire RG58 cable for high frequent measured data and signals defined characteristic impedance and tight production tolerances in 75 Ohm. Shieldin: Tinned copper braiding & aluminum foil

Inner conductor material:	CU, tinned
Dielectric:	cellular PE
Outer conductor material:	braiding CU, tinned
Material outer sheath:	PVC grey, Ø 4.65 mm

Art.-No.	Description
91258.x	Coaxial Cable Thin Wire RG58 C/U, 50 Ohm, double shielded