

U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® SHZ	52023717 14.11.2013

With incised sealing ring for adjustment to several cable diameters
 High strain relief
 Robust
 For cables with large outer diameters



Optimum strain relief



Robust

Application range

Compact brass cable gland for reliable strain relief, solid, for large cable diameters.

Design

PG connection thread

Note

SKINDICHT® SHZ-XL is similar to the SKINDICHT® SHZ, but has an extended connection thread for thick walls

Refer to SKINDICHT® EV for additional accessories

Counter nut to be used: SKINDICHT® SM

Remark

Photographs are not to scale and do not represent detailed images of the respective products.


Technical Data

Article designation / size:	SHZ 9
Clamping range ØF (mm):	7,5 - 8,5
Max. fitting size for installation (mm):	25
SW1/SW2 mm:	17 / 17
Overall length, C (mm):	43
Thread length, D (mm):	10
Pieces / PU:	50
Caution:	The installation dimensions can be found in appendix T21
Material:	Body: nickel-plated brass Sealing: CR O-ring: NBR
Protection rating:	IP 55
Temperature range:	-20°C to +80°C



Product Management	Document: SKINDICHT® SHZ	1 / 2
--------------------	--------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 LAPP GROUP
	SKINDICHT® SHZ	52023717 14.11.2013



Product Management	Document: SKINDICHT® SHZ	2 / 2
--------------------	--------------------------	-------