


► (RT) Standard Bayonet Type
RTMS-M03-L100-K02 (1000)




- Max. operating temperature : -50 C / +400 C
- Standard cable types : Fiber glass + fiber glass + braided wire
- Sensor type : DIN/EN60751 Class "B" 1xPT-1000
- Protection tube material : AIS304 (DIN1.4301) Stainless Steel

► Technical drawing



PT-1000 Connections



- Diameter (M) : 3 mm
- Immersion Length (L) : 100 mm
- Cable Length (K) : 2 m