




Schlauchtüllen, kurz

	Anschluss A	Hex mm	L mm	Ausführung	Artikelnummer
	4 mm für G 3/8		31	Messing	STP17/04
	6 mm für G 3/8		36	Messing	STP17/06
	6 mm für G 3/8		36	1.4305	STP17/06R
	6 mm für G 3/8		36	1.4404	STP17/06E
	9 mm für G 3/8		36	Messing	STP17/09
	9 mm für G 3/8		36	1.4305	STP17/09R
	9 mm für G 3/8		36	1.4404	STP17/09E
	6 mm für G 1/2		38	Messing	STP21/06
	9 mm für G 1/2		38	Messing	STP21/09
	9 mm für G 1/2		38	1.4305	STP21/09R
	9 mm für G 1/2		38	1.4404	STP21/09E
	* UR13/9 erforderlich	13 mm für G 1/2		44	Messing

Schlauchtüllen, lang

	Anschluss A	Hex mm	L mm	Ausführung	Artikelnummer
	4 mm für G 1/4		47	Messing	STD13/04
	6 mm für G 1/4		47	Messing	STD13/06
	4 mm für G 3/8		47,5	Messing	STD17/04
	6 mm für G 3/8		47,5	Messing	STD17/06
	9 mm für G 3/8		47,5	Messing	STD17/09
nach DIN EN 560					


Gewindetüllen

	Anschluss A	Hex mm	L mm	Ausführung	Artikelnummer
	M 5, 3 mm	7	15,5	Messing	GT05/03
	M 5, 3 mm	7	15,5	1.4305	GT05/03R
	M 5, 3 mm	7	15,5	1.4404	GT05/03E
	M 5, 4 mm	7	15,5	Messing	GT05/04
	M 5, 4 mm	7	15,5	1.4305	GT05/04R
	M 5, 4 mm	7	15,5	1.4404	GT05/04E
	M 6, 4 mm	8	23	Messing	GT06/04
	G 1/8, 4 mm *	14	28	Messing	GT10/04
	G 1/8, 4 mm *	14	28	1.4305	GT10/04R
	G 1/8, 4 mm *	14	28	1.4404	GT10/04E
	G 1/8, 6 mm *	14	33	Messing	GT10/06
	G 1/8, 6 mm *	14	33	1.4305	GT10/06R
G 1/8, 6 mm *	14	33	1.4404	GT10/06E	

mit Außengewinde
(* mit Innenkonus 45°)

Gewindetüllen

	Anschluss A	Hex mm	L mm	Ausführung	Artikelnummer
	G 1/8, 8 mm *	14	33	Messing	GT10/08
	G 1/8, 9 mm *	14	33	Messing	GT10/09
	G 1/8, 9 mm *	14	33	1.4305	GT10/09R
	G 1/8, 9 mm *	14	33	1.4404	GT10/09E
	G 1/4, 4 mm *	17	29,5	Messing	GT13/04
	G 1/4, 4 mm *	17	29,5	1.4305	GT13/04R
	G 1/4, 4 mm *	17	29,5	1.4404	GT13/04E
	G 1/4, 6 mm *	17	34,5	Messing	GT13/06
	G 1/4, 6 mm *	17	34,5	1.4305	GT13/06R
	G 1/4, 6 mm *	17	34,5	1.4404	GT13/06E
	G 1/4, 8 mm *	17	34,5	Messing	GT13/08
	G 1/4, 9 mm *	17	34,5	Messing	GT13/09
	G 1/4, 9 mm *	17	34,5	1.4305	GT13/09R
	G 1/4, 9 mm *	17	34,5	1.4404	GT13/09E
	G 1/4, 13 mm *	17	34,5	Messing	GT13/13
	G 3/8, 6 mm *	19	36	Messing	GT17/06
	G 3/8, 6 mm *	19	36	1.4305	GT17/06R
	G 3/8, 6 mm *	19	36	1.4404	GT17/06E
	G 3/8, 8 mm *	19	36	Messing	GT17/08
	G 3/8, 9 mm *	19	36	Messing	GT17/09
	G 3/8, 9 mm *	19	36	1.4305	GT17/09R
	G 3/8, 9 mm *	19	36	1.4404	GT17/09E
	G 3/8, 13 mm *	19	42	Messing	GT17/13
	G 3/8, 13 mm *	19	42	1.4305	GT17/13R
	G 3/8, 13 mm *	19	42	1.4404	GT17/13E
	G 1/2, 6 mm *	24	39	Messing	GT21/06
	G 1/2, 9 mm *	24	39	Messing	GT21/09
	G 1/2, 9 mm *	24	39	1.4305	GT21/09R
	G 1/2, 9 mm *	24	39	1.4404	GT21/09E
	G 1/2, 13 mm *	24	45	Messing	GT21/13
	G 1/2, 13 mm *	24	45	1.4305	GT21/13R
	G 1/2, 13 mm *	24	45	1.4404	GT21/13E
	G 3/4, 13 mm *	32	48,5	Messing	GT26/13
	G 3/4, 16 mm *	32	56,5	Messing	GT26/16
	G 3/4, 19 mm *	32	56,5	Messing	GT26/19
	G 1, 25 mm *	36	67,5	Messing	GT33/25



mit Außengewinde
(* mit Innenkonus 45°)