



## POTTING BOX STYLE A




BOX

## LID STYLE A



COVER

## POTTING BOX STYLE B



BOX

Order code	Mfrs Part No.	TYPE	External dimensions (mm)				
			L	W	H	T1	T2
30-0700	G202013B	BOX	20	20	13	09	1.0
30-0704	G252525B	BOX	25	25	25	1.1	1.1
30-0706	G302015B	BOX	30	20	15	1.1	1.5
30-0714	G404020B	BOX	40	40	20	1.5	1.7
30-0716	G453015B	BOX	45	30	15	1.0	1.6
30-0718	G453025B	BOX	45	30	25	1.0	1.6
30-0722	G505015B	BOX	50	50	15	1.6	1.6
30-0724	G505025B	BOX	50	50	25	1.6	1.6
30-0726	G505050B	BOX	50	50	50	1.6	1.6
30-0728	G705020B	BOX	70.5	50.5	20	1.5	1.9
30-0730	G705035B	BOX	70.5	50.5	35	1.5	1.9
30-0732	G906020B	BOX	90	60	20	1.6	1.9
30-0734	G1005025B	BOX	100	50	25	1.5	1.9
30-0736	G10010040B	BOX	100	100	40	2.0	2.1
30-0738	G202013L	COVER	20	20	13	09	1.0
30-0740	G252515L	COVER	25	25	15	1.1	1.1
30-0742	G302015L	COVER	30	20	15	1.1	1.5
30-0746	G404013L	COVER	40	40	13	1.4	1.7
30-0748	G453015L	COVER	45	30	15	1.0	1.6
30-0752	G505015L	COVER	50	50	15	1.6	1.6
30-0754	G705020L	COVER	70.5	50.5	20	1.5	1.9
30-0756	G906020L	COVER	90	60	20	1.6	1.9
30-0760	G10010040L	COVER	100	100	40	2.0	2.1
			A	B	C	T1	
30-4228	G383839B	BOX	38.8	38.8	39	1.3	
30-4231	G464640B	BOX	46	46	40.5	1.6	
30-4220	G212112B	BOX	21	21	12	1.1	
30-0702	G252515B	BOX	25	25	15	1.1	
30-4230	G453016B	BOX	45.5	30.5	16	1.4	