

Kvalitet / Quality / Qualität:
880

Vægt / Weight / Gewicht	g/m²	240	EN 12127
Komposition / Composition / Gewebemischung	%	100 polyester + PU laminat	
Konstruktion / Construction / Webkonstruktion	3/1 twill		

STYRKE / PHYSICAL PROPERTIES / FESTIGKEIT

Slidstyrke / Abrasion resistance / Strapazierfähigkeit 12 kPa	t	100.000	EN ISO 12947-2
Brudstyrke, kæde / Tensile, warp/ Bruchfestigkeit, Kette	N.	1.100	EN ISO 13394-1
Brudstyrke skud / Tensile, weft/ Bruchfestigkeit, Schuss	N.	900	EN ISO 13394-1
Rivstyrke, kæde / Tearing strength, warp/ Reissfestigkeit, Kette	N.	40	ISO 4674/A1
Rivstyrke, skud / Tearing strength, weft/ Reissfestigkeit, Schuss	N.	40	ISO 4674/A1

FARVEÆGTHEDER / COLOUR FASTNESS / FARBECHTHEIT

Vaskeægted afsmitning / Fastness to washing staining / Waschechtheit Anbluten	Note	4-5	ISO 105-C06
Svedægted afsmitning/ Fastness to perspiration staining/ Schweißechtheit Anbluten	Note	4	ISO 105-E04
Gnidægted, våd / Fastness to rubbing, wet / Reibechtheit, nass	Note	4-5	ISO 105-X12
Gnidægted, tør / Fastness to rubbing, dry / Reibechtheit, trocken	Note	4-5	ISO 105-X12

GENERELLE EGENSKABER / CHARACTERISTICS IN GENERAL / ALLGEMEINE EIGENSCHAFTEN

Dimensionsstabilitet / Dimensional stability / Dimensionsstabilität	%	+/- 1	ISO 6330
Dimensionsstabilitet / Dimensional stability / Dimensionsstabilität	%	-	ISO 15797
Certifikater / Certificates / Zertifikate			
Vaskesymboler/ Carelabel/ Pflegesymbole			
Vandsøjle / Water resistance / Wassersäule	mm H ₂ O	> 4.000	ISO 20811
Åndbarhed / Water vapour permeability / Atmungsaktivität	g/m ² /24 hrs	5.000	CUP METHOD
Finish / Finish / Ausführung	water and soil repellent		

Bemærkninger / Remarks / Bemerkungen:

based on: 10188

date period: 1/1-12 => 19/6-14

int. IPV

Date: 20-02-2015