PATCHCORDS/MOLDED CABLES

Audio and Video Patchcord, and Molded Cables Series 🕄 1/4", Mil-Type, TT or Bantam, Video Series

Part Number	Туре	Plug Finger	Description
Audio Patchcords			
18QD18	1/4" Mil-Type	Brass	2 foot, black nylon jacket
18QF18	1/4" Mil-Type	Brass	3 foot, black nylon jacket
18QH18	1/4" Mil-Type	Brass	4 foot, black nylon jacket
20QD20N*	1/4" Mil-Type	Nickel	2 foot, nylon jacket
20QF20N*	1/4" Mil-Type	Nickel	3 foot, nylon jacket
20QH20N* Uses 2 cond. shield	1/4" Mil-Type ded cable	Nickel	4 foot, nylon jacket
TT122	TT or Bantam	Brass	1 foot, molded gray jacket
TT124	TT or Bantam	Brass	2 foot, molded gray jacket
TT126	TT or Bantam	Brass	3 foot, molded gray jacket
TT127	TT or Bantam	Brass	4 foot, molded gray jacket
TT128	TT or Bantam	Brass	5 foot, molded gray jacket
TT122N*	TT or Bantam	Nickel	1 foot, molded
TT124N*	TT or Bantam	Nickel	2 foot, molded
TT126N*	TT or Bantam	Nickel	3 foot, molded
TT127N*	TT or Bantam	Nickel	4 foot, molded
TT128N*	TT or Bantam	Nickel	5 foot, molded
TT742N*	TT or Bantam	Nickel	1 foot, nylon jacket
TT744N*	TT or Bantam	Nickel	2 foot, nylon jacket
TT746N*	TT or Bantam	Nickel	3 foot, nylon jacket
TT747N* Uses 2 cond. shield	TT or Bantam ded cable	Nickel	4 foot, nylon jacket
Digital AES/EBU	Patchcords		
DTT122	TT or Bantam	Nickel	1 foot, 110 Ohm, black, molded
DTT124	TT or Bantam	Nickel	2 foot, 110 Ohm, black, molded
DTT126	TT or Bantam	Nickel	3 foot, 110 Ohm, black, molded
DTT128	TT or Bantam	Nickel	5 foot, 110 Ohm, black, molded
DTT133	TT or Bantam	Nickel	10 foot, 110 Ohm, black, molde
DMT122	1/4" Mil-Type	Nickel	1 foot, 110 Ohm, black
DMT124	1/4" Mil-Type	Nickel	2 foot, 110 Ohm, black

			/ 1	
Uses 2 cond.	shielded,	110	Ohm cable	

DMT126

DMT128

Ordering Information Part No. Description Molded MIDI Cables MD3 3 foot, 5 pin DIN, molded black MD6 6 foot, 5 pin DIN, molded black MD10 10 foot, 5 pin DIN, molded black MD15 15 foot, 5 pin DIN, molded black Uses 4 cond., 24 awg, PVC outer jacket, braided shielded cable

1/410-1-1

1/4" Cables				
05AD05	2 foot, mono, male to male			
05AK05	6 foot, mono, male to male			
05AN05	10 foot, mono, male to male			
05AU05	25 foot, mono, male to male			
05AN15	10 foot, mono, male to RA male			
05AN80	10 foot, mono, male to female			
05AU80	25 foot, mono, male to female			
10BF10	3 foot, stereo, male to male			
10BK10	6 foot, stereo, male to male			
10BN10	10 foot, stereo, male to male			
15AK15	6 foot, mono, RA male to RA male			
RCA				
25AF25	3 foot, male to male			
25AK25	6 foot, male to male			
25AN25	10 foot, male to male			
25AK82	6 foot, male to female			
30AK30	0 6 foot, RA male to RA male			
30AN30	0 10 foot, RA male to RA male			
30AR30	15 foot, RA male to RA male			
1/4" to RCA				
05AK25	6 foot, 1/4" male to RCA male			

05AN25 10 foot, 1/4" male to RCA male Uses either single or 2 cond, 22awg, PVC outer jacket, braided shielded cable

* When ordering, add the following for cable color: 0 - Black; 2 - Red; 5 - Green; 6 - Blue

1/4" Mil-Type

1/4" Mil-Type



Nickel

Nickel

3 foot, 110 Ohm, black

5 foot, 110 Ohm, black

5555 North Elston Avenue / Chicago, IL 60630 Phone: 773-792-2700 / Fax: 773-792-2129