

Myriad Pendant Silver - Remote Gear

MYRIAD PENDANT 4000K REMOTE GEAR SWITCHED SILVER
2050692



Product features

- High-end architectural (4000K) neutral white LED pendant with non dimmable driver and remote gear housing, finished in a silver finish (RAL9006)



PRODUCT OVERVIEW

Product name	MYRIAD PENDANT 4000K REMOTE GEAR SWITCHED SILVER
Technology	LED
Mount	Ceiling surface mounting
Environment	Indoor
General application	Hospitality, Office, Retail, Residential & Consumer
ETIM Class	EC001743
Warranty	5 years
Fixture luminous flux (lm)	1093
Luminaire efficacy (lm/W)	109.3
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Beam Angle (°)	30
Total power consumption (W)	10

Myriad Pendant Silver - Remote Gear

MYRIAD PENDANT 4000K REMOTE GEAR SWITCHED SILVER
2050692

Electrical protection	Class II
Control gear mounting	Remote
Dimmable	No
Dimming method	N/A
Housing colour	Silver
IP rating	IP20
IK rating	IK02
Product EAN number	5025768506927

DATA TABLE

General data

Product name	MYRIAD PENDANT 4000K REMOTE GEAR SWITCHED SILVER
Technology	LED
Mount	Ceiling surface mounting
Environment	Indoor
General application	Hospitality, Office, Retail, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001743
Warranty	5 years

Optical data

Fixture luminous flux (lm)	1093
Luminaire efficacy (lm/W)	109.3
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Adjustable chromaticity	N
Beam Angle (°)	30
Distribution type	Symmetric

Electrical data

Total power consumption (W)	10
Mains voltage (V)	220-240V
Electrical protection	Class II
Control gear mounting	Remote
Transformer required	Yes
Dimmable	No
Dimming method	N/A
Drive current (mA)	250
Energy Efficiency Class (A->G) of contained light source	D
Nominal Frequency (Hz)	50/60Hz

Lifetime data

Lifespan L70 B50	50000
------------------	-------

