

90° manual deburring tool, HSS, triple cutter

for universal use up to 1000 N/mm²

ORION[®]

Application:

For producing 90° counterbores and for deburring up to 1000 N/mm².

Execution:

- profile-ground triple-edge countersink with radial relief

Advantage:

- radial relief ensures optimum chip breaking



Art. no.	11511 215
Brand	ORION
Manufacturer Part Number	11511215
Countersink angle	90 Degree
Cutting material	HSS
Surface	Uncoated
Number of cutting edges	3 PCS
Spot-facer diameter	15 mm
Gross Weight	0.100 kg
Product Group	1EH

EAN

4053625033430