

SCXP offset solid carbide boring bar, positive, left

For face and longitudinal turning using CP indexable insert

ATORN[®]



Application

For face and longitudinal turning with CP indexable insert, 80°.

Execution

- Precision-manufactured boring bar, **solid carbide**, with internal cooling, offset, type C, attack angle 95°, tip angle 80°, clearance angle 7°

Advantage

- Universal use for face and longitudinal turning
- Positive geometry for the body ensures low cutting forces

Art. No.	17827 195
ISO name	E 0810J SCXP R/L 05
Min. bore diameter	11 mm
Tapered diameter	8 mm
Shaft diameter	10 mm
Clearance length	36 mm
Length	110 mm
Clamping surface height	9 mm
Programming size	6 mm
Suitable for indexable inserts	CP.. 05T1..
Tool design	Right
DIN	8024

EAN-Code

4050293390285