

## Heavy-duty cabinet without central partition

Optionally with solid sheet metal doors or doors with viewing windows, with drawers and shelves

<sup>®</sup>RasterPlan

### Application:

For a total loading capacity of up to 1.65 t for very heavy loads, particularly suitable for storage of the heaviest tools, such as embossing and punching dies.

### Execution:

- Extremely stable welded steel structure with brazed corners, with or without central partition
- Smooth fronts due to flush overlay doors, opening angle more than 200°, continuous rod guiding
- Doors can be locked simultaneously with a triple-point security cylinder lock, incl. 2 keys
- Cabinet base can carry a load of up to 400 kg

### Delivery:

Additional door designs, e.g. perforated or slotted panel doors and sidewall lining, pull-out blocks for drawers and suitable insert material with compartment dividers, additional group or main keys and further paint colours deliverable upon request.



<b>Art. no.</b>	<b>50047 243</b>
<b>Brand</b>	RASTERPLAN
<b>Manufacturer Part Number</b>	1462.06.2016
<b>Door design</b>	Full-sheet panel
<b>Width</b>	1000 mm
<b>Depth</b>	600 mm
<b>Height</b>	1950 mm
<b>Number of shelves</b>	3 PCS
<b>Shelf width</b>	1000 mm
<b>Shelf depth</b>	600 mm
<b>Load-carrying capacity per shelf</b>	160 kg
<b>Number of drawers</b>	3 PCS
<b>Drawer front height</b>	1 x 100 mm, 2 x 125 mm
<b>Drawer width (inner dimension)</b>	889 mm
<b>Drawer depth (inner dimension)</b>	483 mm
<b>Load-carrying capacity per drawer</b>	110 kg
<b>Pullout type</b>	Full extension
<b>With partition wall</b>	No
<b>Load-carrying capacity</b>	1650 kg
<b>Central locking</b>	Yes
<b>Lock type</b>	Twist-grip lock with three-point fastening
<b>Material</b>	Sheet steel
<b>Colour of front</b>	Gentian blue RAL 5010
<b>Surface</b>	Powder-coated
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Gross Weight</b>	154.000 kg
<b>Product Group</b>	5AC

### EAN

4251142217764