

## Serving trolley with three load areas

Anti-slip coating, load capacity 170 kg



### Execution:

- Electrolytically zinc-plated push handle
- Powder-coated load areas with anti-slip coating
- Height to the top load area: 665 mm
- Spacing between load areas: 240 mm
- Two fixed castors and two swivel castors
- Load capacity: 170 kg

### Advantage:

- Welts on all edges - protect doors and furniture
- Anti-slip coating - secure transport of goods



<b>Art. no.</b>	<b>50291 281</b>
<b>Brand</b>	KONGAMEK
<b>Manufacturer Part Number</b>	KM130-HL
<b>Load-carrying capacity</b>	170 kg
<b>Length</b>	810 mm
<b>Loading surface length</b>	630 mm
<b>Height</b>	870 mm
<b>Loading-surface width</b>	370 mm
<b>Loading surface size</b>	630 x 370 mm
<b>Wheel diameter</b>	100 mm
<b>ESD-capable</b>	No
<b>Material of wheel</b>	Polyurethane
<b>Number of steering rollers</b>	2
<b>With wheel lock</b>	No
<b>Number of fixed rollers</b>	2
<b>Gross Weight</b>	22.500 kg
<b>Product Group</b>	5AT

### EAN

7350050356446