

MASCARET 2

REF 103.1.152 A

SAFETY KNIFE WITH TRIGGER AND AUTOMATIC RETRACTABLE BLADE

Ideal for all handling works and for opening cardboard boxes and packaging.

SAFETY • The blade retracts automatically as soon as it is lifted from the cutting surface regardless of the position of the trigger.



DELIVERED WITH A ROUNDED
EDGE BLADE



Large space to
prevent dust
accumulation
and obstruction



MAXIMAL
SAFETY



LIGHT



ERGONOMIC



FOR RIGHT AND LEFT
HANDED USERS



AVOID MSDs



AUTOMATIC RETRACTA-
BLE BLADE BY SPRING




RESISTANT TO
DETERGENTS

TECHNICAL SHEET

INNOVATION: BLADE WITH A ROUNDED EDGE

SAFETY: BACK-AND-FORTH ACTION. A PRESSURE DIFFERENCE DURING CUTTING ALLOWS THE BLADE TO RETRACT AUTOMATICALLY IN THE KNIFE BODY.



THE PROS



DELIVERED WITH A ROUNDED EDGE BLADE REF 152A.6



LOCKABLE TRIGGER



ERGONOMIC AND LIGHT FOR RIGHT AND LEFT HANDED USERS



STRONG STRETCHING SPRING TESTED FOR MORE THAN 100,000 TIMES

FUNCTIONS



To cut single-wall carton



To cut packaging adhesives



To cut plastic films



To cut thick plastic films, PVB

TRIGGER LOCKING ENHANCED SAFETY



MAGNET

PROMOTES GOOD HOLDING OF THE BLADE ON ITS SUPPORT



OTHER CHARACTERISTICS

- Light (63,5 g).
- Reversible and retractable blade with a spring.
- The blade is held by a magnet.
- Easy blade change.
- Avoid MSDs.

BLADE CHANGE


01/ Remove the front part after the unlocking (bottom-up) of the switchblade on the knife side.




02/ Remove the front part, sliding it forward.



03/ Take out the blade at most, pressing the trigger. Remove carefully the blade through the front.




04/ Introduce a new blade. Release the blade and then the trigger. Put back the front part on the knife.




BLADES

DELIVERED WITH




REF 152A.6 Thk 0,6 mm
Blade made of premium quality steel.


OTHER COMPATIBLE BLADES




REF 152.6 Thk 0,6 mm
Blade made of premium quality steel.




REF 652.6.2 Thk 0,6 mm
Blade made of premium quality steel.




REF 652A.6.2 Thk 0,6 mm
Blade made of premium quality steel.



REF 153.6 Thk 0,6 mm
Blade made of premium quality steel.



REF 653.6.1 Thk 0,6 mm
Blade made of premium quality steel.




REF 852A.7 AF Thk 0,7 mm
ceramic blade.

REF 853.7 AF Thk 0,7 mm
Ceramic blade.

Blade reference	Description	Type	Dimensions (in mm) Length • Width • Thickness	Sharpening angle	Hardness
152A.6	Straight blade with a rounded edge	Premium quality steel	54 x 19 x 0,6	18° - 27°	64,0 Hrc
152.6	Straight blade	Premium quality steel	54 x 19 x 0,6	18° - 27°	64,0 Hrc
652.6.2	Serrated straight blade	Premium quality steel	54 x 19 x 0,6	15° - 28,5°	64,0 Hrc
652A.6.2	Serrated straight blade with a rounded edge	Premium quality steel	54 x 19 x 0,6	15° - 28,5°	64,0 Hrc
153.6	Straight blade	Premium quality steel	60 x 19 x 0,6	18° - 28°	64,0 Hrc
653.6.1	Serrated straight blade	Premium quality steel	60 x 19 x 0,6	18° - 32°	64,0 Hrc
852A.7 AF	Serrated straight blade with a rounded edge	Ceramic	55 x 19 x 0,7	16°	-
853.7 AF	Straight blade	Ceramic	59 x 19 x 0,7	16°	-

TECHNICAL SHEET (in mm)



Packaging	Weight PKG	Dimensions (in mm) Length • Width • Thick.	Quantity PKG	Units	Accessories	Material	Colors
SKIN PACK	63,5 g	166 x 59 x 26	10	12 units	Body (2 sides)	PA6 GF 30	Grey
					Spring 25 mm	Stainless Steel	Metal
					Spring 10 mm	Stainless Steel	Metal
					Rod	POM	Orange
					Slider	POM	Orange
					Trigger	POM	Orange
					Latch	POM	Orange
					Lock	POM	Orange
					Blade-holder	POM	Orange
					Trap	PA6 GF 30	Grey
Blade 152A.6	Premium quality steel	Metal					

Patented design.

MP
MURE & PEYROT

MURE & PEYROT
25, rue Roger Touton • BP 50120
Parc d'Activités Bordeaux Nord
33041 BORDEAUX CEDEX - FRANCE

Tel.: +33 (0)556 693 200 / Fax: +33 (0)556 693 202 / E-mail: mail@mure-peyrot.com

FOR MORE INFORMATION
MURE-PEYROT.COM