


Pluggable Terminal Blocks

Clamp Terminal 5.08 mm Pitch



FEATURES:

Standard

Polarised mouldings

Withstand Voltage - AC2000V/1Min

Guided pin alignment

cUL approved

SPECIFICATION:

Pitch	5.08 mm
Gender housing	Female
Connection direction	vertical
Connection cross-section	0.33-2 mm ² (22-14AWG)
Colour	green
Rated voltage to EN	300 V
Rated current to EN	15 A
Rated voltage to UL	300 V
Rated current to UL	15 A
Temperature range	-40...+105 °C

PRODUCT RANGE:

Art. no.	Pole no.	Termination type
RND 205-00364	2	Screw Connection
RND 205-00365	3	Clamp Terminals/Screw Connection
RND 205-00366	4	Clamp Terminals/Screw Connection
RND 205-00367	5	Clamp Terminals/Screw Connection
RND 205-00368	6	Clamp Terminals/Screw Connection
RND 205-00370	8	Clamp Terminals/Screw Connection
RND 205-00371	9	Clamp Terminals/Screw Connection