


**RoHS COMPLIANT**

**SPECIFICATIONS:**

1. RATING: 11V AC 1A MAX  
OR 12V DC 2A MAX.
2. INSULATION RESISTANCE:  
50M OHM MIN AT 500V DC.
3. DIELECTRIC STRENGTH:  
500V AC / 1 MINUTE.



	7.0 $\phi$ BACK SHELL
	6.0 $\phi$ BACK SHELL
X	5.0 $\phi$ BACK SHELL (STANDARD)
	COVER DIM.

**TABLE A**

**MATERIAL:**  
 A. COVER: PE+2L  
 B. SHELL: ABS  
 C. METAL SHIELD:  
 BRASS NICKEL PLATED  
 D. HOUSING: NYLON66+CF  
 E. CONTACT:  
 BRASS SILVER PLATED