



2855

Wire Twisting Pliers with Phosphate Finish

PRODUCT DETAILS

- Capacity: Wires up to Ø1.04 mm for the 2855 and Ø1.6 mm for the 2855 D
- High-performance alloy steel
- Phosphate finish, anti-corrosion treated
- To secure with wire fasteners in critical applications and exposed to vibration
- Consistent and fast wire twisting saves time
- Can be used for any wire length and any twist length
- Use by first gripping the wire, then pull the spinner knob to get the turning action
- When the pliers grip the wire, any number of twists can be made by pulling out and pushing in the spinner knob
- The reversible models eliminate the need of a second tool just a simple twist of the patented reversing sleeve gives right or left-hand capability
- The smaller model is appropriate to be used in confined areas
- Jaws angled at 30°, serrated and with cutter



PRODUCT ATTRIBUTES

Product								
2855	232 mm	24,2 mm	16,2 mm	10,6 mm	4 mm	2.5 mm	9 mm	240 g
2855 D	287 mm	29 mm	20 mm	10.5 mm	5 mm	4 mm	10 mm	450 g

Follow the Fish!

