

# Pomona®

## Model 3840 Adapter, BNC (Male), Resistor Termination





#### **MATERIALS:**

Body: Brass, Center Contact: Gold plated brass

Outer Contact: Tarnish Resistant gold plated Beryllium Copper.

Dielectric: Teflon

Gasket/Seals: Silicone rubber Resistor: Deposited carbon film Marking: "Pomona 3840"

Label: "TERM, \*Ω 1/2W"

#### **RATINGS:**

Frequency Range: DC to 500 MHz

Resistance Tolerance: ± 1% Power: 1/2W @ 70°C Max

### ORDERING INFORMATION: Model 3840-\*

\*= Resistance Value 50, 75, 93, 100, 600 Ordering Example: 3840-50 = 50 Ohms

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02$ " (,51 mm),  $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

6/9/99 SY/EH/LS Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060 Pomona*ACCESS* **90210** (800) 444-6785 or (425) 446-6010 More drawings available at www.pomonaelectronics.com